


**8773**


# Mobile tower with stabiliser



**The new flexible safety powerhouse:** Optional assembly with height offset, for example in stairwell position. Spacious platforms with non-slip surface and manual safety hooks – no accidental locking into place during assembly or dismantling. With four height-adjustable swivel castors.

**Features:**

- **Work platform: 2.45 x 1.30 m**
- **Castors: Ø 200 mm**
- **Permissible load: 150 kg/m<sup>2</sup> (1.5 kN/m<sup>2</sup>)**



Reach height (approx. m)	3.40	4.40	5.40	6.40	7.40	8.40	9.40	10.40	11.40	12.40	13.40
Tower height (approx. m)	2.64	3.64	4.64	5.64	6.64	7.64	8.64	9.64	10.64	11.64	12.64
Standing height (approx. m)	1.40	2.40	3.40	4.40	5.40	6.40	7.40	8.40	9.40	10.40	11.40
Platform length (approx. m)	2.45	2.45	2.45	2.45	2.45	2.45	2.45	2.45	2.45	2.45	2.45
Frame section width (approx. m)	1.50	1.50	1.50	1.50	1.50	1.50	1.50	1.50	1.50	1.50	1.50
<b>Ballasting</b>											
Indoor, centre (kg)	0	0	0	0	0	0	0	0	0	0	0
Indoor, on wall (kg)	0	0	0	20 <sup>(1)</sup>	20 <sup>(1)</sup>	30 <sup>(1)</sup>	40 <sup>(1)</sup>	50 <sup>(1)</sup>	60 <sup>(1)</sup>	70 <sup>(1)</sup>	90 <sup>(1)</sup>
Outdoor, centre (kg)	0	40	0	0	0	40	not permitted	not permitted	not permitted	not permitted	not permitted
Outdoor, on the wall (kg)	0	40	30 <sup>(1)</sup>	50 <sup>(1)</sup>	0 <sup>(2)</sup>	0 <sup>(2)</sup>	170 <sup>(2)</sup>	not permitted	not permitted	not permitted	not permitted
Order no.	877303	877304	877305	877306	877307	877308	877309	877310	877311	877312	877313

<sup>(1)</sup> Ballasting is not required when using two wall connectors (607141) for pressure support.

<sup>(2)</sup> Two wall connectors (607141) need to be used for pressure support.

Required additional parts from page 23.

Individual parts and parts list can be found in the instructions for assembly and use on page 67. | [Click here.](#)